

# **Series AK 1100 ABSOLUTE PRESSURE REGULATOR**

LOW FLOW - SUB-ATMOSPHERIC

- ♦ Vacuum to 300 psig (21 bar) inlet, 100 mm Hg absolute outlet
- Flow rate to 500 sccm
- Stainless Steel or Brass construction
- Ni-Cr-Mo alloy internals, 'SH' option, for added corrosion resistance
- High leak integrity
- Machined from bar stock
- Optional accessories
- Fine adjustment control (six turns of the knob from off to wide open)
- Cleaned for O2 service
- Field repairable
- Diffusion resistant Stainless Steel diaphragm
- Knob LOTO option (refer to AP KL data sheet)
- Installation and operating instructions available at www.aptech-online.com



#### ENGINFERING DATA

## **Operating Parameters**

Source pressure 300 psig (21 bar) Delivery pressure 100 mm Hg absolute to 10 psig Proof pressure 150% of operating pressures Burst pressure 300% of operating pressures

### **Other Parameters**

Leak rate

Inlet /outlet ports 1/4" NPT; 1/4" & 3/8" compression

(optional porting available)

Flow coefficient, Cv 0.05

0.49 in<sup>3</sup> (8 cm<sup>3</sup>)

Internal volume -40° to +160°F (-40° to +71°C)\* Operating temperature

1 x 10<sup>-9</sup> sccs

#### **M**ATERIALS OF CONSTRUCTION

Body Poppet and diaphragm

Seat **Bonnet**  **AK 1100B** brass SS 316 PCTFE (Polyimide and PEEK $^{\circledR}$  Opt) SS 303

**AK 1100S** SS 316L SS 316

PCTFE (Polyimide and PEEK Opt) SS 303


**AK 1100SH** 


SS 316L Ni-Cr-Mo alloy / UNS N06022

PCTFE (PEEK Opt) SS 303

\*VS option 14° to 194°F (-10° to + 90°C). All specifications subject to change without notice.


PEEK® Victrex Manufacturing LTD





All dimensions in inches (mm).
Metric dimensions are for reference only.

#### **Porting Configurations**



NOTE: Brass only available with 4PL or 5PC porting.

CAUTION: Product selection is the sole responsibility of the user, regardless of any recommendations or suggestions made by the factory. The user shall make selections based upon their own analysis and testing with regard to function, material compatibility and product ratings. Proper installation, operation and maintenance are also required to assure safe, trouble free performance.

ORDERING INFORMATION					
AK 1101	S	3P	4 4	0	P
Series	Material	Port	1 2	3 4 5	Options
		Configuration	Ports	Ports (Gauge/Accessory)	
AK 1101= 100 mm Hg to 10 psig		2P = 2 Ports	4 = 1/4 inch NPT	0 = No gauge or	P = Panel installation*
		3P = 3 Ports	4T = 1/4 inch	device installed	CGA = Inlet fitting 320, 330,
		4P = 4 Ports	compression	V3 = 30-0-30 psig/bar	350, 580, 660, 678
S = Stainless steel (SS)		4PL = 4 Ports	6T = 3/8 inch	1 = 30-0-100 psig/bar	VS = Polyimide seat
SH = SS with Ni-Cr-Mo alloy internals		5PC = 5 Ports	compression	2 = 0-200 psig/bar	PK = PEEK seat
B = Brass				4 = 0-400 psig/bar	KL = Knob LOTO (refer to
					AP KL data sheet)
			NOTE: Designators required for all ports, but "0" not required		*Panel hole 1.42 diameter.
			if there isn't a port. A 2P has designators only for ① & ② ports, as example AK 1101 S 2P 44 not AK 1101 S 2P 44 000.		

AP Tech has product options and variations which are not documented in data sheets. If you have a model number that is not defined by the ordering information, please consult the factory or your local representative.